

Resolute™ Strength Line

Introduction

Resolute™ Selectorized (RSL) is a new line of 21 commercial selectorized strength products which will replace and refresh the existing Discovery Selectorized line.

Assembly

The units ship boxed and require assembly. They will arrive in multiple boxes, generally four boxes per machine (five for larger units). If assembling on site, ensure adequate recycling/trash bins are available for packaging removal (cardboard, plastics, foam).

Assembly hardware is metric. Technicians should have a full set of metric sockets and wrenches for assembly.

Assembly guides will ship with the unit. Care should be taken when unboxing to gather all parts and pieces prior to disposing of any packaging. Assembly guides can also be found on each unit's product page at Precor.com.

Assembly videos are available for each unit. Videos are posted and can be viewed on Precor Connect.



Once assembled, review the Final Checklist in the assembly guide to verify the unit is assembled properly, bolts are torqued as directed, the unit is level, and the unit pulleys, rods, and cables all operate smoothly.

Preventative maintenance

All Resolute™ Selectorized units have daily, weekly, monthly and yearly preventative maintenance tasks. Specific cleaning liquids and lubricants are noted in the maintenance guide.

The Resolute™ Maintenance Guide can be found [here](#). Note that, when applicable, only Teflon® lubricants should be used. Petroleum based lubricants can cause damage to the Polymeric bushings used on these units.